












PCB LAYOUT

SPECIFICATION:
MATERIAL:
HOUSING: LCP 30% G/F UL 94V-0
COLOR:BLACK
CONTACT: PHOSPHOR BRONZE C2680 H,T=0.25mm
PEG: BRASS C2680R H,T=0.30mm
SHELL: spcc,T=0.30mm
FINISH:
CONTACT: G/F GOLD/TIN PLATING ON CONTACT AREA
100u" MIN. Matte TIN PLATING ON SOLDER TAILS
50u" MIN. NICKEL UNDERPLATING OVERALL
PEG:100u" MIN. Matte TIN PLATING ON SOLDER TAILS
50u" MIN. NICKEL UNDERPLATING OVERALL
SHELL:100u" MIN. Matte TIN PLATING ON SOLDER TAILS
50u" MIN. NICKEL UNDERPLATING OVERALL

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-SATA-01-7PSZG	版本 REV.	A
			X. ±0.30	X.* ±3°					品名 TITLE	SATA 7P公座双柱AB型带铁壳成品	页次 SHEET	1/1
			X.X ±0.20	X.X* ±2°					客户料号 CUTM.NO.			
			X.XX ±0.05	X.XX* ±0.5°					审核 CHECK			
		批准 APPROVAL	JOHN									
		单位 UNITS				MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			