



技术指标(Technical Index):

- 1.工作温度(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):50V DC/AC(rms).
- 3.额定电流(Rated current):1.5A,AC/DC(AWG#28).
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Dielectricwithstanding voltage):500V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 100\text{M}\Omega$.
- 7.适用线规(Apply to gauge):AWG28#~AWG30#
(O.D 0.5mm-0.7mm).

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		
			X.±0.50	±1°				
			.X±0.20		审核 CHECK	EVA		
			.XX±0.10		核准 APPROVAL	JADE		
					单位 UNITS	MM	比例 SCALE	1:1

P/N		材质	镀层
BX-MX1.2-DZ		磷青铜	镀锡
料号 PART NO.	BX-MX1.2-DZ	版本 REV.	A
品名 TITLE	1.2Pitch B型电池座公头端子	页次 SHEET	1/1
客户料号 CUTM.NO.			

B Bossie (博锡)