






RECOMMEND PCB LAYOUT
PCB TOLERANCE:±0.05



NOTES:
1.MATERIAL:
HOUSING:LCP 30% G/F UL94V-0
COLOR:BLACK
CONTACT:BRASS T=0.25mm
2.FINISH:
CONTACT:GOLD FLASH PLATING ON CONTACT AREA
100u"MIN.TIN PLATING ON SOLDERTAILS
50u"MIN.NICKEL UNDERPLATING OVER ALL
BOARD LOCK:100u"MIN.TIN PLATING ON SOLDERTAILS
50u"MIN.NICKEL UNDERPLATING OVER ALL
3.ELECTRICAL:
CURRENT RATING:1.5 AMPERE PER CONTACT
CONTACT RESISTANCE:30 MΩ MAX
INSULATION RESISTANCE:1000 MΩ MIN
DIELECTRIC WITH STANDING VOLTAGE:500 VDC
OPERATING TEMPERATURE: -40°C ~ +85°C



环保要求		产品必须符合ROHS要求			制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-SATA-01-15PSZG		版本 REV.	A
3	Peg	Brass C2680		Tin/Ni Plated				X. ±0.30	X.* ±3°	审核 CHECK	LEO			品名 TITLE	SATA 15P公座90度DIP型带鱼叉针长2.30mm		页次 SHEET	1/1
2	Terminal	Brass C2680		Gold/Tin Plated				X.X ±0.20	X.X* ±2°	核准 APPROVAL	JOHN			客户料号 CUTM.NO.				
1	Housing	High Temp	Black	UL 94V-0				X.XX ±0.05	X.XX* ±0.5°									
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK						单位 UNITS	MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.				