




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2025.06.10	阿树
A2	ECN-P-2026091101	(A2)X4	产品结构及尺寸变更	2026.09.11	山楂




Technical Date
Pin(outer sleeve):Brass,machined CuZn38pb2
Clip (Contact 4 Finger):Beryllium copper,heat teated
Insulator:PBT UL94V-0 colour:black
Tin Plated:2um"/80u"Ni,5um"/200u"SN
Gold Plated:2um"/80u"Ni,GF
Current rating:3Amps
Contact resistance: 10mΩ Max
Dielectric strength: Min 1000V RMS
Operating temperature:-40°C~+105°C



PART NO.:
X5621 F V-2xXX-C762 D1220
① ② ③ ④ ⑤ ⑥
①Series No
②Category:F-Female
③Welding Board Angle:V-Stright 180°
④Row No-Pin No:2xXX-2x06~2x08Pin
⑤Line spacing:C=7.62mm
⑥Pin Length:D=12.20mm

poles	Dimensions(mm)	
	A	B
2x06	15.24	12.70
2x08	20.32	17.78



Recommended P.C.B
Layout(±0.05)

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



X5621FV-2xXX-C762D1220	PBT	Brass	Tin Gold 1u	X5621W
PART NO	Material	Material(Pin)	Finshl(Terminal)	Suitable XKB Wafer
DESIGN	山楂	VIEW:	MODEL TYPE: 2.54mm BTB Style Connector	
CHECKED		UNIT: mm/in	PART NO.: X5621FV-2xXX-C762D1220	
APPROVED		SIZE: A4	DWG NO.:	
SCALE			PAGE	REVISION
N/A			1/1	A2

XKB INDUSTRIAL PRECISION CO.,LIMITED