









SPECIFICATION:

1.MATERIAL:


HOUSING:LCP 30% G/F UL 94V-0
COLOR:BLACK
CONTACT:BRASS C2680R-H,T=0.25mm

2.FINISH:

CONTACT:1u",3u",5u",15u"30u"GOLD PLATING ON CONTACT AREA
100u" MIN.TIN PLATING ON SOLDER TAILS
40u" MIN.NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:

CURRENT RATING:1.5 AMPERE PER CONTACT
CONTACT RESISTANCE:30 MILLIOHMS MAX
INSULATION RESISTANCE:1000 MEGOHMS MIN
DIELECTRIC WITH STANDING VOLTAGE:500 VDC
OPERATING TEMPERATURE: -40°C ~ +85°C



P.C.B Layout

环境要求		产品必须符合ROHS要求			制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-SATA-02-22PXTG		版本 REV.	A
2	Terminal	BRASS C2680R-H		Gold/Tin Plated				X.±0.30	X.*±3°	审核 CHECK	EVA		品名 TITLE	SATA 7+15P 夹角公差 夹板1.0七孔		页次 SHEET	1/1
1	Housing	High Temp	Black	UL 94V-0				.X±0.20	.X*±2°	核准 APPROVAL	JADE		客户料号 CUTM.NO.				
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK						单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)			