










RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE:±0.05

SPECIFICATION:

1.MATERIAL:

HOUSING: LCP UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:

CONTACT:1~15u" GOLD PLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

环境要求		产品必须符合ROHS要求			制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-SATA-08-22PSTMP2	版本 REV.	A
3	Peg	Brass C2680		Tin/Ni Plated				X.±0.30	X.*±3°	审核 CHECK	EVA		品名 TITLE	SATA 7+15P 带SMT接口 H:4.20 板下垫脚	页次 SHEET	1/1
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated				.X±0.20	.X*±2°	核准 APPROVAL	JADE		客户料号 CUTM.NO.			
1	Housing	High Temp	Black	UL 94V-0				.XX±0.05	.XX*±0.5°		单位 UNITS	MM	比例 SCALE	1:1		
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK												