



- 1.工作温度(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage): 250V DC/AC(rms) .
- 3.额定电流(Rated current): $9.5\text{A(AWG\#16}\sim\text{\#18)}$ AC,DC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Dielectricwithstanding voltage): 1500V AC/minute .
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 7.适用线规(Apply to gauge):T1:AWG\#16~\#18.
T2:AWG\#20~\#24.

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-MX3.0-2-GDZ-XM2	版本 REV.	A
			X. ±0.50	±1°	审核 CHECK	LEO			品名 TITLE	MX3.0公头端子(大电流)	页次 SHEET	1/1
			X.X ±0.20		核准 APPROVAL	JOHN			客户料号 CUTM.NO.			
			X.XX ±0.10						单位 UNITS	MM	比例 SCALE	1:1