

1.MATERIAL:

COLOR:BLACK

PEG: BRASS C2680R-H,T=0.30mm






2.FINISH:

100u" TIN PLATING ON SOLDERTAILS


30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL



RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE:±0.05

环保要求		产品必须符合ROHS要求			制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-SATA-05-22PSTMP2		版本 REV.	A		
3	Peg	Brass C2680R-H		Tin/Ni Plated				X.±0.30	X.*±3°	审核 CHECK	EVA			品名 TITLE	SATA 7+15P 母座板下SMT H7.50叁叉侧插式		页次 SHEET	1/1		
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated				.X±0.20	.X*±2°	核准 APPROVAL	JADE			客户料号 CUTM.NO.						
1	Housing	High Temp	Black	UL 94V-0				.XX±0.05	.XX*±0.5°											
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK						单位 UNITS	MM	比例 SCALE	1:1							
1		2			3			4		5		6		7		8			9	