

1. MATERIAL:

COLOR:BLACK

PEG: BRASS C2680R-H,  $T=0.30\text{mm}$







2. *FINISH:*

## 100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

# PEG:100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL



| 环保要求 |             | 产品必须符合ROHS要求        |       |                 | 制图<br>DRAWN | 变更内容<br>DESCRIPTION | 日期<br>DATE | GENERAL TOLERANCE |             | 制图<br>DRAWING | ROSE        |                |      | 料号<br>PART NO.                                                                                                                                            | ZX-SATA-07-22PSTMP2 |                                | 版本<br>REV. | A |             |     |                                                                                       |  |  |  |
|------|-------------|---------------------|-------|-----------------|-------------|---------------------|------------|-------------------|-------------|---------------|-------------|----------------|------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|--------------------------------|------------|---|-------------|-----|---------------------------------------------------------------------------------------|--|--|--|
| 3    | Peg         | Brass C2680         |       | Tin/Ni Plated   |             |                     |            | X. ±0.30          | X.* ±3°     |               | 审核<br>CHECK | LEO            |      |                                                                                                                                                           | 品名<br>TITLE         | SATA 7+15P 母座 SMT H:6.74 板下型侧插 |            |   | 页次<br>SHEET | 1/1 |                                                                                       |  |  |  |
| 2    | Terminal    | Pho.Bronze C5191R-H |       | Gold/Tin Plated |             |                     |            | X.X ±0.20         | X.X* ±2°    |               |             | 批准<br>APPROVAL | JOHN |                                                                                                                                                           |                     | 客户料号<br>CUTM.NO.               |            |   |             |     |  |  |  |  |
| 1    | Housing     | High Temp           | Black | UL 94V-0        |             |                     |            | X.XX ±0.05        | X.XX* ±0.5° |               |             |                |      |                                                                                                                                                           |                     |                                |            |   |             |     |                                                                                       |  |  |  |
| NO.  | DESCRIPTION | MATERIAL            | COLOR | REMARK          |             |                     |            |                   |             | 单位<br>UNITS   | MM          | 比例<br>SCALE    | 1:1  |  兆星精密电子（深圳）有限公司<br>ShenZhen ZhaoXing Precision electronics Co., Ltd. |                     |                                |            |   |             |     |                                                                                       |  |  |  |
| 1    |             | 2                   |       | 3               |             | 4                   |            | 5                 |             | 6             |             | 7              |      | 8                                                                                                                                                         |                     | 9                              |            |   |             |     |                                                                                       |  |  |  |