

RoHS Compliant

A

B

C

D

E









A

B

C

D

E



MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)		联晟欣连接器 (深圳) 有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24
X. ±0.25		CHECKED		DATE	
X.x ±0.20		APPROVED		DATE	
X.xx ±0.15		PART NO: LCK670B50069A		REV: 04	SCALE: 1:1
ANGULAR ±3°		DRAWING NO: 102022802		SIZE: A4	UNIT: mm
				SHEET: 1/1	

1

2

3


4

5



6

7

RoHS Compliant



RECOMMENDED PCB LAYOUT
TOLERANCE ± 0.05 (焊盘推荐图)
(FOR REFERENCE ONLY)



3D VIEW

NOTES:

1:MATERIAL:

1-1:COPPER ALLOY THICKNE=0.10mm

2:FINISH:

2-1:SEE DETAILED LIST.

3:PRODUCT SPECIFICATIONS:

3-1:RATED CURRENT:1.5A/MAX

3-2:VOLTAGE RATING:5.00V/AC/DC/MAX

3-3:CONTACT RESISTANCE:50m Ω /MAX

3-4:OPERATING TEMPERATURE:-40°C~85°C

3-5:NORMAL FORCE OF PRESS@0.55mm:20g ± 10 g.

3-6:DURABILITY:10,000 CYCLES.

4:SALT SPRAY:SEE DETAILED LIST.



5:PACKING SPECIFICATION:REEL&TARE

6:DIMENSIONS MARKED $\square$, CPK>1.33

7:ALL DIMENSIONS MARKED $\blacktriangledown$ MUST BE CONTROLLED BY QC;

8:COMPLIANT TO RoHS&LEAD FREE

9:PART NO.;



MEASURE POINT:
QUADRANT POINT $\square$
TANGENCY POINT $\square$
INTERSECTION POINT $\square$

UNLESS OTHERWISE
SPECIFIED, TOLERANCE:

X. ± 0.25
X.x ± 0.20
X.xx ± 0.15
ANGULAR $\pm 3'$

QP
TP
IP

联晟欣连接器(深圳)有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN Andy DATE 2014.12.24

CHECKED DATE

APPROVED DATE

PART NO: LCK670B50069A

DRAWING NO: 102022802

TITLE:
充电弹片L3.00xW1.50xH6.70
Shielding Clip,SMT

REV: 04 SCALE: 1:1 UNIT: mm

SIZE: A4 SHEET: 1/1