






RoHS Compliant




SEE DETAIL:B
SCALE 2/1




SEE DETAIL:B




吸嘴尺寸参考
NozzleDIM./Reference



SECTION:A-A






SEE DETAIL:C
SCALE 2/1





MEASURE POINT: QUADRANT POINT TANGENCY POINT INTERSECTION POINT		GP TP IP	联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE:			DESIGN	Andy	DATE	2014.12.24
X.		±0.25	CHECKED		DATE	
X.x		±0.20	APPROVED		DATE	
X.xx		±0.15	PART NO: LCK427BA0220A			
ANGULAR		±3°	DRAWING NO: 102022802			
TITLE: 充电弹片L2.77xW1.34xH4.27 Shielding Clip,SMT				REV: 04	SCALE: 1:1	UNIT: mm
				SIZE: A4	SHEET: 1/1	

RoHS Compliant



3D VIEW



NOTES:

(1):MATERIAL:

1-1:STAINLESS STEEL THICKNE=0.10mm

(2):FINISH:

2-1:REFER TO THE SPECIFICATION DESCRIPTION TABLE.

2-2:DIMENSIONS OF PCB PAD STENCIL ARE FOR REFERENCE ONLY,
CUSTOMER CAN MODIFY IT BY THEIR OWN.

(3):PRODUCT SPECIFICATIONS:

3-1:RATED CURRENT:1.5A/MAX

3-2:VOLTAGE RATING:5.0V/AC/DC/MAX

3-3:CONTACT RESISTANCE:50m Ω /MAX

3-4:OPERATING TEMPERATURE:-40°C~85°C

3-5:NORMAL FORCE OF PRESS 0.57MM:0.28 ± 0.1 N.

3-6:DURABILITY:10,000 CYCLES.

(4):SALT SPRAY:48 HOURS(JUST BY ALL OUTSIDE AREA)

(5):PACKING SPECIFICATION:REEL&TARE

(6):DIMENSIONS MARKED ,CPK> 1.33

(7):ALL DIMENSIONS MARKED MUST BE CONTROLLED BY QC;

(8):COMPLIANT TO RoHS&LEAD FREE

MEASURE POINT:

QUADRANT POINT

TANGENCY POINT

INTERSECTION POINT

UNLESS OTHERWISE
SPECIFIED,TOLERANCE:

X. ± 0.25

X.x ± 0.20

X.xx ± 0.15

ANGULAR $\pm 3^\circ$



联晟欣连接器(深圳)有限公司

Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24
CHECKED		DATE	
APPROVED		DATE	

PART NO: LCK427BA0220A

DRAWING NO: 102022802

TITLE:
充电弹片L2.77xW1.34xH4.27
Shielding Clip,SMT

REV: 04

SIZE: A4

SCALE: 1:1

SHEET: 1/1

