









RoHS Compliant



RECOMMENDED PCB LAYOUT
TOLERANCE ± 0.05 (焊盘推荐图)



3D VIEW



NOTES:

1:MATERIAL:

1-1:TITANIUM COPPER THICKNE=0.10mm

2:FINISH:

2-1:SEE DETAILED LIST.

3:PRODUCT SPECIFICATIONS:

3-1:RATED CURRENT:1.5A

3-2:VOLTAGE RATING:5.0V.

3-3: CONTACT RESISTANCE: 50mOHM MAX

AFTER DURABILITY AND ENVIRONMENT: $\Delta R=20\text{m}\Omega$

3-4: OPERATING TEMPERATURE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$

3-5: NORMAL FORCE: REFER TO THE FORCE PROFILE.

3-6:DURABILITY:20,000 CYCLES. YIELD NO EXCEED 0.1MM.

4:SALT SPRAY:48 HOURS(JUDGED BY ALL OUTSIDE AREA)

5:PACKING SPECIFICATION:REEL&TARE

6: DIMENSIONS MARKED , CPK > 1.33

7: DIMENSIONS MARKEDW "▼" IS KEY DIMENSION.

8:COMPLIANT TO RoHS&LEAD FREE

9:PART NO.;

MEASURE POINT:		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd
QUADRANT POINT	Ⓚ	
TANGENCY POINT	Ⓜ	
INTERSECTION POINT	Ⓜ	
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		
X. ±0.25		
X.xx ±0.20		
X.xxx ±0.15		
ANGULAR ±3°		