


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	NEW DRAWING	2026.06.10	Janus



LED COLOR P/N TABLE

LED ITEM	Left	Right
0	Non	Non
1	Green	Yellow
2	Yellow	Green
3	Green/Yellow	Green/Yellow
4	Green/Orange	Green/Orange
5	Green	Green/Yellow
6	Green	Green/Orange

SPECIFICATION:

Electrical:

Current Rating:1.5Amp max @25℃

Voltage Rating:150VAC max

Insulation Resistance:500 megohms min

Contact Resistance:20 milliohms max(Initial)

Withstanding Voltage:1000 VAC

Mechanical:

Durability:750 Cycles

Operating Temperature:-40℃~+70℃

Storage Temperature:-50℃~+75℃

Contact Normal Force:100g Minimum

Material:

Housing: Thermoplastic UL94V-0,PBT




Shield:0.15mm Thickness Stainless Steel SUS304-1/2H Plated Ni

Contact:0.45mm Dia Phosphor Bronze


Plated Gold Over Ni

For wave Soldering Temperature: 260+/-5℃,5sec/95%Areabe covered


Withstand Temperature: 230+/-5℃,5sec No stick tin melting phenomenon



LED SCHEMATIC



PCB LAYOUT/TOP VIEW



P/N: 102012-021121

02:RJ45

SERIES NUMBER

XX: 001~999

SERIES NO.1,2,3...

LED COLOR:SEE TABLE

CONTACT PLATED

1: G/F AU

TAIL SOLDER PLATED

1: G/F AU


PACKAGING:2:TRAY

MAGNETIC:0:NON

TOLERANCE	NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10°	PART NO.	TITLE: RJ45 1X1 8P8C Tab Up L15.75mm Lock TYPE		
.XX ±0.20	.X.* ± 8°		DRAWG NO. C-102012		
.XXX ±0.10	.XX.* ± 5°				
UNITS	mm	DESIGN: Arvin	SCALE 1:1	SHEET 1/3	REV. A
MATERILA		CHED:			
FINISH		APPD:			


- 1-1. 將成品放入底盤凹槽中, 並注意成品擺放方向的一致性(如示意圖一);
- 1-2. 每盤TRAY放滿, 一盒100PCS成品, 注意不可少放或錯放;

- 2-1. 將每盤裝入成品的底盤(如示意圖一), 蓋上上蓋, 再依照《貼標規範》要求粘貼標籤;
- 2-2. 成品置於TRAY中, 注意TRAY(一上蓋配置一底盤)堆疊需朝同一方向(成品外觀形狀一致)擺放. 并排相疊至10盤(共1000PCS)如示意圖三.



示意圖一
底盒
100PCS/盤


示意圖二
上蓋




示意圖三

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING		XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD				
X.X	±0.30	X.*	±10°	PART NO.	TITLE: RJ45 1X1 8P8C Tab Up L15.75mm Lock TYPE			
.XX	±0.20	.X.*	± 8°					
.XXX	±0.10	.XX.*	± 5°					
UNITS		mm		DESIGN:	Arvin			
MATERILA				CHEd:	DRAWG NO. C-102012			
FINISH				APPD:				
						SCALE	SHEET	REV.
						1:1	2/3	A


- 3-1. 將產品套入防水袋,再放入1包乾燥劑. 將防水袋整齊折合, 如示意圖四;
- 3-2. 將產品裝入紙箱, 如示意圖五;
- 3-3. 用膠帶把紙箱封合, 如示意圖六, 並按《貼標規範》要求粘貼標籤;



示意圖四



示意圖五



条码标签（具体样式依客户标准）

示意圖六

包 裝 容 量		
PCS/TRAY	PCS/內箱	PCS/外箱
100	/	1000

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING		XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD				
X.X	±0.30	X.*	±10°	PART NO.	TITLE: RJ45 1X1 8P8C Tab Up L15.75mm Lock TYPE			
.XX	±0.20	.X.*	± 8°		DRAWG NO. C-102012			
.XXX	±0.10	.XX.*	± 5°					
UNITS		mm		DESIGN:	Arvin			
MATERILA				CHED:	SCALE 1:1 SHEET 3/3 REV. A			
FINISH				APPD:				