







1 2 3 4 5 6 7 8 9 10 11




General Specification
Current Rating: 1.5A DC /Contact, 20mA DC for LED signals
Voltage Rating: 125V AC /Contact, 2.0 volts DC for LED signals
Operating Environment
Standard Temperature: -20℃~+70℃
Industrial Temperature: -40℃~+85℃
Humidity: 20~70%
Contact Resistance: ≤30mΩ
Insulation Resistance: ≥50MΩ
Dielectric Strength: 500V AC/(50HZ)/Min
Mating And Unmating Force: 3~20N
Durability: 750 Cycles Min

Material Specification
Housing :Thermo-plastic, UL94V-0.
Contact :Alloy Copper
Shield : Alloy Copper

Please refer to the customer drawing when customer has specified



PCB LAYOUT
RECOMMENDED



网络插座外形图



温州瑞川电子有限公司
WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

3	插针	PHOSPHOR BRONZE	16	0.8U"	
2	后盖	PA66	2	BLACK	
1	塑座	PA46	1	BLACK	
序号	名称	材料	数量	镀层/颜色	备注

绘图:	吴家飞	日期:	2022.11.05	品名:	RJ45-62-42-12(全塑无灯)
审核:	陈伟	日期:		料号:	524212-80000010AB30 (WR44198)
核准:	陈伟	日期:		型号:	RJ45
日期:				图号:	

一般公差	30~	±0.20	10~30	±0.20	±0.15	角度:	±2°	版本:	1 of 1	单位:mm	比例: 1:1	纸张: A4	印
审核:	陈伟	日期:		型号:	RJ45	图号:		版本:	1 of 1	单位:mm	比例: 1:1	纸张: A4	印
核准:	陈伟	日期:		型号:	RJ45	图号:		版本:	1 of 1	单位:mm	比例: 1:1	纸张: A4	印
日期:				型号:	RJ45	图号:		版本:	1 of 1	单位:mm	比例: 1:1	纸张: A4	印