








REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	NEW DRAWING	2026.06.10	Janus



RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05

- NOTE:
- MATERIAL:
 - HOUSING: PBT L94V-0 BLACK
 - CONTACT: $\varnothing 0.46\text{mm}$ COPPER ALLOY
 - SHELL: $T=0.2\text{mm}$, COPPER ALLOY
 - FINISH:
 - CONTACT: G/F PLATED OVER Ni
 - SHELL: PLATING Ni OVERALL
 - ELECTRICAL:
 - CONTACT CURRENT RATING: 1.5A MIN.
 - VOLTAGE RATING :125V AC (rms)
 - WITHSTANDING VOLTAGE: 1000 VAC
 - INSULATION RESISTANCE: 500 MEGAOHMS MIN.
 - CONTACT RESISTANCE: 30 MILLIOHMS MAX.
 - ENVIRONMENTAL :
 - OPERATING TEMPERATURE: -40°C TO +85°C
 - STORAGE TEMPERATURE: -40°C TO +85°C



P/N: 102003-021121

02:RJ45

SERIES NO.1,2,3...

LED COLOR:SEE TABLE

CONTACT PLATED

1: G/F Au

TAIL SOLDER PLATED

1: G/F Au

PACKAGING:2:TRAY

MAGNETIC:0:NON

SERIES NUMBER

XX: 001~999

LED COLOR P/N TABLE		
LED ITEM	Left	Right
0	Non	Non
1	Green	Yellow
2	Yellow	Green
3	Green/Yellow	Green/Yellow
4	Green/Orange	Green/Orange
5	Green	Green/Yellow
6	Green	Green/Orange

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10°	PART NO.	TITLE: RJ45 1X1 Vertical 空包弹 H=16.75mm W LED Lock TYPE			
.XX ±0.20	.X* ± 8°	DESIGN: Arvin	DRAWG NO. C-102003			
.XXX ±0.10	.XX* ± 5°	CHED:				
UNITS	mm	APPD:				
MATERILA						
FINISH						
				SCALE 1:1	SHEET 1/1	REV. A