






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	NEW DRAWING	2026.06.10	Janus



- NOTES:
- ELECTRICAL:
1. VOLTAGE RATING: 125V AC.
 2. CURRENT RATING: 1.5A.
 3. CONTACT RESISTANCE: 30 mΩ MAX.
 4. INSULATION RESISTANCE: 500 MΩ MIN @ 500V DC.
 5. DIELECTRIC STRENGTH: 1000V AC 50Hz or 60Hz, 1MIN.
- MECHANICAL:
1. INSERT MATERIAL: PBT UL94V-0 BLACK.
 2. CONTACT MATERIAL: DIAMETER 0.46mm C51000 (QSn4-0.3) PHOSPHOR BRONZE GOLD PLATING OVER NICKEL.
 3. SHIELD: 0.20mm THICKNESS H65Y BRASS NICKEL PLATED.
 4. MATING/UNMATING FORCE: 2.2KG.F MAX.
 5. RETENTION STRENGTH: 5.0KG.F MIN BETWEEN JACK AND PLUG.
 6. OPERATING LIFE: 750 CYCLES MIN.
- ENVIRONMENTAL:
1. STORAGE: -40℃ ~ +85℃ RELATIVE HUMIDITY<70%.
 2. OPERATION: -40℃ ~ +85℃.



LED L YELLOW LED R GREEN
9 10 11 12

P/N: 102010-021121

02:RJ45

SERIES NO.1,2,3...

LED COLOR:SEE TABLE

CONTACT PLATED
1: G/F AU


TAIL SOLDER PLATED
1: G/F AU

PACKAGING:2:TRAY

MAGNETIC:0:NON

SERIES NUMBER

XX: 001~999



LED COLOR P/N TABLE		
LED ITEM	Left	Right
0	Non	Non
1	Green	Yellow
2	Yellow	Green
3	Green/Yellow	Green/Yellow
4	Green/Orange	Green/Orange
5	Green	Green/Yellow
6	Green	Green/Orange

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10°	PART NO.	TITLE: RJ45 JACK 8P8C			
.XX ±0.20	.X* ± 8°	DESIGN: Arvin	DRAWG NO. C-102010			
.XXX ±0.10	.XX* ± 5°					
UNITS	mm	CHED:				
MATERILA		APPD:				
FINISH				SCALE 1:1	SHEET 1/1	REV. A