






General Specification
Current Rating:1.5A DC /Contact, 20mA DC for LED signals
Voltage Rating:125V AC /Contact, 2.0 volts DC for LED signals
Operating Environment
Standard Temperature: -20℃~+70℃
Industrial Temperature: -40℃~+85℃
Humidity: 20~70%
Contact Resistance:≤30mΩ
Insulation Resistance:≥500MΩ
Dielectric Strength:500V AC/(50HZ)/Min
Mating And Unmating Force:3~20N
Durability:750 Cycles Min

Material Specification
Housing :Thermo-plastic, UL94V-0.
Contact :Alloy Copper
Shield :Alloy Copper
Please refer to the customer drawing when customer has specified



网络插座外形图



温州瑞川电子有限公司
WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

序号	名称	材料	数量	镀层/颜色	备注
1	插座	PA46	1	BLACK	
2	插针	PHOSPHOR BRONZE	8	0.8U"	

一般公差
30~ ±0.20
10~30 ±0.20
~10 ±0.15
角度: ±2°

品名: RCH-52-10(无耳)
料号: 5210-80000011AB31 (WR44196)
型号: RJ45
图号:

版本: 1 of 1
单位:mm
比例: 1:1
纸张: A4

网络插座外形图

图号: 5210-80000011AB31 (WR44196)

料号: 5210-80000011AB31 (WR44196)

型号: RJ45

版本: 1 of 1

温州瑞川电子有限公司

品名: RCH-52-10(无耳)

料号: 5210-80000011AB31 (WR44196)

型号: RJ45

版本: 1 of 1