

1

2

3

4

5

6

7

8

SAMZO

REAC/ROHS

REV

ECN NO

DESRPTION

DESIGN

APPROVAL

DATE

A1

NEW

Replace frame

2019.06.12

E

D

C

B

A

26,3

11

14±0.5

11

24,6

BNC-JKW-263-W0-N

Surface treatment镀层:亮镍

Pin position脚位:卧式90° 转接头

Length体长:26.3mm

Product number编号:JKW

Product series系列:BNC同轴射频天线座

Technical Requirements

1. Frequency: 0~3 GHz

2. Impedance: 50 Ω

3. VSWR: ≤ 1.35

4. Operating Voltage: 500 V

5. Withstand Voltage: 1500 V

6. Insulation Resistance: ≥ 5000 MΩ

7. Contact Resistance: Inner conductor ≤ 1.5 mΩ

Outer conductor ≤ 1 mΩ

8. Insertion Loss: ≤ 0.3 dB

9. Unspecified tolerances shall be ±0.2

ITEM

DESCRIPTION

MATERIAL

QTY

FINSH/COLOR

C

插孔

HPB59-1

1

-----

B

绝缘体

聚四氟乙烯

1

-----

A

主体

黄铜

1

镀镍

DESIGN

WANGGUIFA

2018.06.12

≥2~5<

±0.25

CHECKED

ZHENGUILAN

2018.06.12

≥0~2<

±0.15

APPROVED

LILIANJIANG

2018.06.14

≥5

±0.35

1

2

3

4

5

6

7

8

FIRST VIEW

SCALE

1:1

UNIT

mm

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.

WWW.SANCNN.COM

TITLE: BNC-JKW

BNC公转母90度 L型弯式转接头

DWG NO: BNC263-P001

PART NO: BNC263-061400

MODEL NO: BNC-JKW-263-W0-N

NAME: BNC COAXIAL RF CONNECTOR

SAMZO COMPONENTS

Electronic switch and connector manufacturer