






PCB LAYOUT
(TOP VIEW)



General Specification
Current Rating:1.5A DC /Contact, 20mA DC for LED signals
Voltage Rating:125V AC /Contact, 2.0 volts DC for LED signals
Operating Environment
Standard Temperature: -20℃~+70℃
Industrial Temperature: -40℃~+85℃
Humidity: 20~70%
Contact Resistance:≤30mΩ
Insulation Resistance:≥500MΩ
Dielectric Strength:500V AC/(50HZ)/Min
Mating And Unmating Force:3~20N
Durability:750 Cycles Min

Material Specification
Housing :Thermo-plastic, UL94V-0.
Contact :Alloy Copper
Shield :Alloy Copper
Please refer to the customer drawing when customer has specified

网络插座外形图



温州瑞川电子有限公司
WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

序号	名称	材料	数量	镀层/颜色	备注
4	LED灯	树脂/CU	2	NI/Sn 80U°	铜灯
3	后盖	PBT	1	BLUE	
2	插针	PHOSPHOR BRONZE	8	FU°	
1	塑座	PBT	1	BLUE	

绘图: 吴鹏飞 日期: 2023.5.18

审核: 陈伟 日期:

核准: 陈伟 日期:

一般公差	品名:	RCF-52-42A(带灯全塑) 绿正负 黄负正
30~	料号:	5242A-86Y20010PU22-1 (WR50046)
10~30	型号:	RJ45
~10	图号:	
角度: ±2°	单位:mm	比例: 1:1
页面: 1 of 1	版本:	纸张: A4

温州瑞川电子有限公司

版本: A/0

变更履历

变更单号

该图面供温州瑞川电子有限公司内部使用,不得私自复印