









REV.	ECN NO OR DESCRIPTION	REVISED	DATE

备注:

1. 胶芯材质: LCP BLACK UL94-V0
2. 端子材质: C5210-EH, 镀镍底30u", 触点镀金1u", 焊脚镀雾锡120u".
3. 固定片材质: SUS201-3/4H, 镀镍底30u", 整体镀雾锡120u".
4. 有标示 ▼ 的为QC及IPQC之检验重点
5. 有标示 ⊗ 的为FAI检验尺寸
6. 有标示 ⊠ 的为变更处记号



RECOMMENDED PCB LAYOUT
TOL:(±0.05)



PART No.	料号
BAT-03P30H54Y	有柱
BAT-03P30H54W	无柱







UNLESS OTHERWISE SPECIFIED TOLERANCES		 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD				
DECIMALS:		ANGLES:		TITLE 3.0PH 内焊式 5.4H 无柱电池座		
X	:±0.35	X	:±2°	DWN	xiong	PART NO. BAT-03P30XXX
X.X	:±0.25	X.X	:±1°	CHKD	lee	SCALE:1:1 UNIT: mm 
X.XX	:±0.15	APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
CUSTOMER COPY						



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

备注:

- 胶芯材质:LCP BLACK UL94-V0
- 端子材质:C5210-EH, 镀镍底30u", 触点镀金1u", 焊脚镀雾锡120u".
- 固定片材质:SUS201-3/4H, 镀镍底30u", 整体镀雾锡120u".
- 有标示 ▼ 的为QC及IPQC之检验重点
- 有标示 ⊗ 的为FAI检验尺寸
- 有标示 ⊠ 的为变更处记号



PART No.	料号
BAT-03P30H54Y	有柱
BAT-03P30H54W	无柱

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.35 X :±2°
X.X :±0.25 X.X :±1°
X.XX :±0.15








东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD


TITLE	3.0PH 肉焊式 5.4H 有柱电池座			
DWN	xiong	PART NO.	BAT-03P30XXX	
CHKD	lee	SCALE:1:1	UNIT: mm	⊗
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
CUSTOMER COPY				



REV.	ECN NO OR DESCRIPTION	REVISED	DATE



- 备注:
1. 胶芯材质: LCP BLACK UL94-V0
 2. 端子材质: C5210-EH, 镀镍底30u", 触点镀金1u", 焊脚镀雾锡120u".
 3. 固定片材质: SUS201-3/4H, 镀镍底30u", 整体镀雾锡120u".
 4. 有标示 ▼ 的为QC及IPQC之检验重点
 5. 有标示 ⊗ 的为FAI检验尺寸
 6. 有标示 ⊠ 的为变更处记号




PART No.	料号
BAT-03P30H60Y	有柱
BAT-03P30H60W	无柱





UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	3.0PH 内焊式 6.0H 无柱电池座		
X :±0.35	X :±2°	DWN	xiong	PART NO. BAT-03P30XXX	
X.X :±0.25	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm
X.XX :±0.15		APVD	wang	SIZE: A4	SHEET:10F 1
CUSTOMER COPY					
		REV: A4			



REV.	ECN NO OR DESCRIPTION	REVISED	DATE



- 备注:
1. 胶芯材质:LCP BLACK UL94-V0
 2. 端子材质:C5210-EH, 镀镍底30u", 触点镀金1u", 焊脚镀雾锡120u".
 3. 固定片材质:SUS201-3/4H, 镀镍底30u", 整体镀雾锡120u".
 4. 有标示 ▼ 的为QC及IPQC之检验重点
 5. 有标示 ⊗ 的为FAI检验尺寸
 6. 有标示 ⊠ 的为变更处记号



PART No.	料号
BAT-03P30H60Y	有柱
BAT-03P30H60W	无柱

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:		TITLE			
X	:±0.35	3.0PH 内焊式 6.0H 有柱电池座			
X.X	:±0.25	DWN	xiong	PART NO. BAT-03P30XXX	
X.XX	:±0.15	CHKD	lee	SCALE:1:1	UNIT: mm
		APVD	wang	SIZE: A4	SHEET:10F 1
		CUSTOMER COPY			