









| REV. | ECN NO OR DESCRIPTION | REVISED | DATE |
|------|-----------------------|---------|------|
|      |                       |         |      |
|      |                       |         |      |



- 注解:
1. 素材要求:
    - 1.1 胶芯: LCP 30%GF, 防火等级: UL94V-0. 颜色: 黑色;
    - 1.2 端子: C5191-H, T=0.15MM
    - 1.3 外壳: SUS201 1/2H, T=0.20MM
  2. 电镀要求:
    - 2.1 端子: 接触区镀金1U", 焊脚区域镀锡100~120U", 全部区域电镀镍底50U".
  3. 电气性能要求:
    - 3.1 额定电流 1.0A. 额定电压 30V
    - 3.2 耐压交流电压最小100VAC.
    - 3.3 绝缘电阻最小100M 欧姆.
    - 3.4 接触电阻最大50毫欧.
  4. 环境性能要求:
    - 4.1 使用环境-30摄氏度~80摄氏度
    - 4.2 部件耐热焊接温度符合230摄氏度30~60秒, 260摄氏度10秒要求.
  5. "△" 为QC重点量测尺寸
  6. "⊗" 为FAI量测尺寸
  7. 部件符合RHOS 2005/95/EC.

| pin number | pin name |
|------------|----------|
| G1         | switth   |
| pin 8      | RSV      |
| pin 7      | DO       |
| pin 6      | VSS      |
| pin 5      | SCLK     |
| pin 4      | VDD      |
| pin 3      | DI       |
| pin 2      | CS       |
| pin 1      | RSV      |




TABLE A:

| 规格    | DIM A | DIM B | 料号         |
|-------|-------|-------|------------|
| H2.3  | 2.3   | 0.75  | TF-110H23  |
| H2.45 | 2.45  | 0.9   | TF-110H245 |
|       |       |       |            |
|       |       |       |            |
|       |       |       |            |
|       |       |       |            |

|                                          |                                    |                                                                                                                                                      |             |  |                                                                                       |  |
|------------------------------------------|------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|--|---------------------------------------------------------------------------------------|--|
| UNLESS OTHERWISE<br>SPECIFIED TOLERANCES |                                    | <div></div> 东莞市汉博电子科技有限公司<br>DONGGUAN HANBO TECHNOLOGY CO., LTD |             |  |                                                                                       |  |
| DECIMALS:      ANGLES:                   |                                    | TITLE   MICRO SD 避空短体TF卡2.3H有侦测PIN                                                                                                                   |             |  |                                                                                       |  |
| X        :±0.30    X        :±2°         | DWN    xiong    PART NO. TF-110H23 |                                                                                                                                                      |             |  |                                                                                       |  |
| X.X      :±0.20    X.X    :±1°           | CHKD   lee    SCALE:1:1            |                                                                                                                                                      | UNIT:   mm  |  |  |  |
| X.XX    :±0.10                           | APVD   wang    SIZE: A4            |                                                                                                                                                      | SHEET:10F 1 |  | REV: A4                                                                               |  |
|                                          |                                    | CUSTOMER COPY                                                                                                                                        |             |  |                                                                                       |  |