





General Specification
Current Rating:1.5A DC /Contact, 20mA DC for LED signals
Voltage Rating:125V AC /Contact, 2.0 volts DC for LED signals
Operating Environment
Standard Temperature: -20℃~+70℃
Industrial Temperature: -40℃~+85℃
Humidity: 20~70%
Contact Resistance:≤30mΩ
Insulation Resistance:≥500MΩ
Dielectric Strength:500V AC/(50Hz)/Min
Mating And Unmating Force:3~20N
Durability:750 Cycles Min

Material Specification
Housing :Thermo-plastic, UL94V-0.
Contact :Alloy Copper
Shield :Alloy Copper

Please refer to the customer drawing when customer has specified



网络插座外形图

序号	名称	材料	数量	键层/颜色	备注
5	LED灯	树脂/FB	2	NI/AG	
4	后盖	PA46	1	BLACK	
3	插针	PHOSPHOR BRONZE	8	0.8U"	
2	外壳	H62	1	NI	
1	塑座	PA46	1	BLACK	

 温州瑞川电子有限公司
WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

图:	吴昊飞	日期:	2023.7.12	一般公差		品名:	RCH-52-42(带灯后脚3.8)绿黄负正		
审核:	司清编	日期:		30~ ±0.25		料号:	522-2-9C718011AB33 (WR50168)		
批准:	朱华	日期:		10~30 ±0.20		型号:	RJ45		
校:		日期:		~10 ±0.15		单位:mm	比例: 1:1	纸张: A4	
		日期:		角度: ±2°		版本:	图号:	20210804-03	
		日期:		1 of 1					