



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	NEW DRAWING	2026.06.10	Janus

E



LED COLOR P/N TABLE

LED ITEM	Left	Right
0	Non	Non
1	Green	Yellow
2	Yellow	Green
3	Green/Yellow	Green/Yellow
4	Green/Orange	Green/Orange
5	Green	Green/Yellow
6	Green	Green/Orange

SPECIFICATION:

Electrical:

Current Rating:1.5Amp max @25℃
Voltage Rating:150VAC max
Insulation Resistance:500 megohms min
Contact Resistance:30 milliohms max
Withstanding Voltage:1000 VAC





Mechanical:

Durability:750 Cycles
Operating Temperature:-40℃~+70℃
Storage Temperature:-50℃~+75℃
Contact Normal Force:100g Minimum

Material:

Housing:PBT Black UL94V-0
Shield: 0.15mm Thickness SUS304 Ni Plated
Contact:0.45mm Dia Phosphor Bronze
Plated Gold Over Ni
Soldering Temperature: 260+/-5℃,5sec/95%Areabe covered
Withstand Temperature: 270+/-5℃,5sec No stick
tin melting phenomenon

D



P.C.B LAYOUT

P/N: 102006-021101

02:RJ45

SERIES NUMBER

XX: 001~999

SERIES NO.1,2,3...

LED COLOR:0:NON-LED

CONTACT PLATED

1: G/F AU

TAIL SOLDER PLATED

1: G/F AU

PACKAGING:2:TRAY

MAGNETIC:0:NON

TOLERANCE	NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10°	PART NO.	TITLE: RJ45 1X1 8P8C Tab Down L18.4mm Lock TYPE		
.XX ±0.20	.X* ± 8°		DRAWG NO. C-102006		
.XXX ±0.10	.XX* ± 5°				
UNITS	mm	DESIGN: Arvin			
MATERILA		CHED:			
FINISH		APPD:			
			SCALE	SHEET	REV.
			1:1	1/3	A

E

D


C

B


A

- 1-1. 將成品放入底盤凹槽中, 並注意成品擺放方向的一致性(如示意圖一);
- 1-2. 每盤TRAY放滿, 一盒100PCS成品, 注意不可少放或錯放;


- 2-1. 將每盤裝入成品的底盤(如示意圖一), 蓋上上蓋, 再依照《貼標規範》要求粘貼標籤;
- 2-2. 成品置於TRAY中, 吸塑盒四周粘上膠帶固定, 注意TRAY(一上蓋配置一底盤)堆疊需朝同一方向(成品外觀形狀一致)擺放. 相疊至10盤2堆(共2000PCS)如示意圖三.



示意圖一
底盒
100PCS/盤




示意圖二
上蓋




示意圖三

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING		XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X	±0.30	X.* ±10°	PART NO.	TITLE: RJ45 1X1 8P8C Tab Down L18.4mm Lock TYPE			
.XX	±0.20	.X.* ± 8°					
.XXX	±0.10	.XX* ± 5°		DRAWG NO. C-102006			
UNITS	mm		DESIGN: Arvin				
MATERILA			CHED:		SCALE	SHEET	REV.
FINISH			APPD:		1:1	2/3	A


- 3-1. 將產品套入防水袋,再放入1包乾燥劑. 將防水袋整齊折合, 如示意圖四;
- 3-2. 將產品裝入紙箱, 如示意圖五;
- 3-3. 用膠帶把紙箱封合, 如示意圖六, 並按《貼標規範》要求粘貼標籤;



示意圖四



示意圖五



条码标签（具体样式依客户标准）

示意圖六

包 裝 容 量		
PCS/TRAY	PCS/內箱	PCS/外箱
100	/	2000

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10°	PART NO.	TITLE: RJ45 1X1 8P8C Tab Down L18.4mm Lock TYPE			
.XX ±0.20	.X.* ± 8°		DRAWG NO. C-102006			
.XXX ±0.10	.XX.* ± 5°					
UNITS	mm	DESIGN: Arvin				
MATERILA		CHED:				
FINISH		APPD:				
				SCALE 1:1	SHEET 3/3	REV. A