








Pin No.	NAME	TYPE	DESCRIPTION
1	DAT 2	I/O/PP	Date Line(bit2)
2	CD/DAT 3	I/O/PP	Card Detect/Date Line(bit3)
3	CMD	PP	Command Response
4	VDD	S	Supply Voltage
5	CLK	I	Colck
6	VSS	S	Supply Voltage Ground
7	DAT0	I/O/PP	Date Line(bit0)
8	DAT1	I/O/PP	Date Line(bit1)



- NOTES:
- MATERIAL:
HOUSING: THERMOPLASTIC, UL 94V-0.
COLOR: BLACK
CONTACT: COPPER ALLOY T=0.15mm
SHIELDED: STAINLESS STEEL T=0.20mm
 - FINISH:
CONTACT: GOLD PLATING ON CONTACT AREA
G/F PLATING ON SOLDER TAILS
50u" MIN. NICKEL UNDERPLATING OVER ALL
SHIELDED: 50u" MIN. NICKEL PLATED OVER ALL
 - PRODUCT SPECIFICATIONS:
VOLTAGE RATING: 30V DC
CURRENT RATING: 0.5A
INSULATION RESISTANCE: 1000 MEG.OHM MIN
CONTACT RESISTANCE: 100 MILL.OHM MAX
OPERATION TEMPERATURE: -20° TO +85°
DURABILITY: 3000 CYCLES

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X : ±0.45 X : ±2°
X.X : ±0.35 X.X : ±1°
X.XX : ±0.25



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	短型 TF CARD 无侦测 H=2.55		
DWN	xiong	PART NO. TF-028-H255	
CHKD	lee	SCALE: 1:1	UNIT: mm
APVD	wang	SIZE: A4	SHEET: 1 OF 1
REV: A4			
CUSTOMER COPY			