


General Specification
Current Rating: 1.5A DC /Contact, 20mA DC for LED signals
Voltage Rating: 125V AC /Contact, 2.0 volts DC for LED signals
Operating Environment:
Standard Temperature: -20°C~+70°C
Industrial Temperature: -40°C~+85°C
Humidity: 20~70%
Contact Resistance: $\leq 30m\Omega$
Insulation Resistance: $\geq 500M\Omega$
Dielectric Strength: 500V AC/(60HZ)/Min
Withstanding Force: 3~20N
Durability: 750 Cycles Min

Material Specification
Housing :Thermo-plastic, UL94V-0,
Contact :Alloy Copper
Shield :Alloy Copper

Please refer to the customer drawing when customer has specified

网络插座外形图

2	插针	PHOSPHOR BRONZE	6	0.80"	
1	插座	PA46	1	BLACK	
序号	名称	材料	数量	镀层/颜色	备注



温州瑞川电子有限公司
WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

图:	吴鹏飞	日期:	2023.3.8	品名:				RCH-52-04(无耳6P6C)			
审核:	周清瑞	日期:		公差							
核准:	李华	日期:		30~							
				±0.25							
				10~30							
				±0.20							
				~10							
				±0.15							
				±0.2°							
				1 of 1							
				版本:							
				料号:				5204-60000011AB33 (WR44288)			
				型号:				RJ45			
				图号:							
				单位:mm				比例: 1:1			
				纸张: A4							