








Rating: 0.5A 30V DC
Contact Resistance:100 mΩ Max.
Operating temperature:-20℃~70℃
Operating force:3~20N
Operating Life:5,000cycles

P.C.B LAYOUT
TOP VIEW



SCHEMATIC



PIN	Ø2.0	Ø2.5
XXX	200	250
APPD.		

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
⑥	PIN	1	BRASS	Ni-Plating
⑤	CURVE PIECE	1	BRASS	Ag-Plating
④	FLAT PIECE	1	BRASS	Ag-Plating
③	SPRING	1	SUS301	Ag-Plating
②	COVER	1	PBT	
①	HOUSING	1	PBT	

APPROVALS		DATE
DRAWN	G.M.Chen	2018/3/15
CHECKED		
APPROVALS		

DEALON 德隆
ELECTRONICS CO.,LTD

ECN NO.		REV.	DATE.	DESCRIPTION.			CHANGE.	CHECK.	APPRO.	TOLERANCES ARE		ANGLE	UNIT: mm	SCALE: 1:1	SHEET 1 OF 1
		A		NEW						30°±0.1	±0.30				
										10~30	±0.20				
										5~10	±0.15	±2°			
										~5	±0.10				
										PART NO.		DC-012A-XXX			
										TITLE:		DC JACK			
										DRAWING NO.					