

RoHS

目錄
MAPX

設 變 內 容
MODIFICATION

日 期
DATE

电气特性:Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗:Contact Resistance
30 milliohms MAX
4. 耐电压:Dielectnrc Withstanding Voitage:
500 V AC AT Sea Levol
5. 绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

1. 插拔力: Cnnector Mate and Unmate Force
Mate force:3.57kgf (MAX)
Unmate force:0.7kgf (MIN)
2. 端子保持力: Terminal Retenion
1.0kgf (MIN)
3. 寿命: 1500次

原材料:Matorial:

1. 塑胶:Housing:pbt /lcp
2. 端子:Contact:Copper Alloy C2680
3. 外壳:Shell:SPCC/c2680

电镀:Finish:

1. 端子Contact: Au G/F u" Plated on contact area
Tin50u" Plated on solder area
Nickel 30u" Plated underplating over all.
2. 外壳Shell: Nickel 50u"Min plating over all.
3. Temperature Range:-55° C to +85° C

PCB LAYOUT

Pin NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND

产品图
PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE			
X.	±0.35	X'	±5'
.X	±0.30	.X"	±2"
.XX	±0.25	.XX"	±1"
.XXX	±0.10	.XXX"	±0.5"



深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位
UNITS

MM

制图
DRAWING

Erick

产品料号
PRODUCT PART NO.

903-241A2031S10100

比例
SCALE

1:1

审核
CHKD

L S S

产品名称
PRODUCT NO.

AF无后盖直脚无边内弹壳壳T型LCP本色SMT

日期
DATE

2021/03/10

核准
APPD

黄国荣

角法
VIEW

版本
VER

40