


RECOMMENDED FPC SPEC
THICKNESS=0.3±0.02mm

SPECIFICATION

- 1.Rating : AC/DC250V 0.5A.
- 2.Contact resistance: $\leq 50m\Omega$.
- 3.Insulation resistance: $\geq 500M\Omega$ (DC500V).
- 4.Withstanding voltage: 500VAC .
- 5.Mating force: 插入力: 拉扣扣入顺畅, 本体不变形
- 6.Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.

邮箱: hooya89@hooya.hk
电话: 0769-82310511-867

	A	B	C	D
4	1.50	2.60	6.50	7.60
5	2.00	3.10	7.00	8.10
6	2.50	3.60	7.50	8.60
7	3.00	4.10	8.00	9.10
8	3.50	4.60	8.50	9.60
9	4.00	5.10	9.00	10.10
10	4.50	5.60	9.50	10.60
11	5.00	6.10	10.00	11.10
12	5.50	6.60	10.50	11.60
13	6.00	7.10	11.00	12.10
14	6.50	7.60	11.50	12.60
15	7.00	8.10	12.00	13.10
16	7.50	8.60	12.50	13.60
17	8.00	9.10	13.00	14.10
18	8.50	9.60	13.50	14.60
19	9.00	10.10	14.00	15.10
20	9.50	10.60	14.50	15.60
21	10.00	11.10	15.00	16.10
22	10.50	11.60	15.50	16.60
23	11.00	12.10	16.00	17.10
24	11.50	12.60	16.50	17.60
25	12.00	13.10	17.00	18.10
26	12.50	13.60	17.50	18.60
27	13.00	14.10	18.00	19.10
28	13.50	14.60	18.50	19.60
29	14.00	15.10	19.00	20.10
30	14.50	15.60	19.50	20.60
31	15.00	16.10	20.00	21.10
32	15.50	16.60	20.50	21.60
33	16.00	17.10	21.00	22.10
34	16.50	17.60	21.50	22.60
35	17.00	18.10	22.00	23.10
36	17.50	18.60	22.50	23.60
37	18.00	19.10	23.00	24.10
38	18.50	19.60	23.50	24.60
39	19.00	20.10	24.00	25.10
40	19.50	20.60	24.50	25.60
41	20.00	21.10	25.00	26.10
42	20.50	21.60	25.50	26.60
43	21.00	22.10	26.00	27.10
44	21.50	22.60	26.50	27.60
45	22.00	23.10	27.00	28.10
46	22.50	23.60	27.50	28.60
47	23.00	24.10	28.00	29.10
48	23.50	24.60	28.50	29.60
49	24.00	25.10	29.00	30.10
50	24.50	25.60	29.50	30.60
51	25.00	26.10	30.00	31.10
52	25.50	26.60	30.50	31.60
53	26.00	27.10	31.00	32.10
54	26.50	27.60	31.50	32.60
55	27.00	28.10	32.00	33.10
56	27.50	28.60	32.50	33.60
57	28.00	29.10	33.00	34.10
58	28.50	29.60	33.50	34.60
59	29.00	30.10	34.00	35.10
60	29.50	30.60	34.50	35.60

					TOLERANCE UNLESS SPECIFIED							
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°						
							NO	DATE	REVISIONS		BY	APPD
4	CONTACTFOOT	PHOSPHOR BRONZE	XX	Sn-Plated	TITLE: FPC,0.5MM			UNIT : MM	ROHS	DWN		
3	METAL	BRASS	2	Sn-Plated	MODEL: 0.5A-LT-10PZ-006			SCALE: 1:1	COMPLIANT	CHK'D		
2	BUTTON	LCP	1		 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司			APPD				
1	HOUSING	LCP	1									
NO.	PART NAME	MATERIAL	QTY	FINISHING				PRO.AGL:  			REV :A0	