











SCHEMATIC



P. C. B LAYOUT



				TOLERANCE UNLESS SPECIFIED							
7	COVER	PPA	1								
6	KNOB	PBT	1								
5	CONTACT	BRONZE	1	Ag-PLATED	UP TO 5mm: ±0.1 ANGULAR ABOVE 5mm: ±0.2 ±1°	1					
4	SPRING	SUS	1			NO	DATE	REVISIONS		BY	APPD
3	LOCK PIN	SUS	1		TITLE: PUSH SWITCH		UNIT : MM	ROHS COMPLIANT	DWN		
2	CASE	PA66	1		MODEL: PB-22E62-S -C		SCALE: 1:1	CHK'D			
1	TERMINAL	BRASS	3	Ag-PLATED	HAOYU(HONGKONG)LIMITED				APPD		
NO.	PART NAME	MATERIAL	QTY	FINISHING	皓宇(香港)有限公司				PRO.AGL:	PRO.AGL: 	REV :A0