




SCHEMATIC

SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100\text{m}\Omega$.
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: C:160 $\pm$ 50gf/D:200 $\pm$ 80gf/E:250 $\pm$ 80gf.
- 6.Travel:0.35 $\pm$ 0.1mm.
- 7.Life test: 100,000 cycles.
- 8.Operation temperature range:-25 $^{\circ}\text{C}$ ~85 $^{\circ}\text{C}$.

邮箱: hooya89@hooya.hk
电话: 0769-82310511-867

防水等级: IP67



P. C. B LAYOUT

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		NO	DATE	REVISIONS		BY	APPD
					<1.5: $\pm 0.1\text{mm}$ >1.5~5.0: $\pm 0.25\text{mm}$ >5.0: $\pm 0.3\text{mm}$	ANGULAR $\pm 1^{\circ}$						
7	TERMINAL	BRASS	1	Ag-PLATED								
6	HOUSING	PPA	1	BLACK								
5	REED	SUS	1	Ag-CLAD								
4	WATERPROOF MEMBRANE	PI	1	YELLOW								
3	GLUE	SILICA GEL	1									
2	COVER	SUS	1									
1	BUTTON	LCP	1									
					TITLE: TACT SWITCH			UNIT : MM		ROHS	DWN	
					MODEL: TC-06107FSB-050E-03			SCALE: 1:1		COMPLIANT	CHK'D	
					DONGGUANG HAOYU ELECTRONICS CO., LTD					APPD		
					皓宇 HOOYA 东莞市弘皓电子有限公司			PRO.AGL:			REV :A0	