





SPECIFICATION

1. Rating : AC125V 0.1A.
 2. Contact resistance : $\leq 100\text{m}\Omega$.
 3. Insulation resistance : $\geq 100\text{M}\Omega$ (DC500V).
 4. Withstanding voltage : 1000VAC .
 5. Operating Force : $30 \pm 20\text{gf}$.
 6. life test : 50,000 cycles.
 7. Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
 8. Sign"" is importance dimension.
 9. RATING : 0.1A 42VDC $\mu 40\text{T}125$ (UL, CUL ; CQC; ENEC)
- 邮箱 : hooya89@hooya.hk
电话 : 0769-82310511-867



P.C.B LAYOUT



				TOLERANCE							
				UNLESS SPECIFIED							
7	KEY	SUS	1								
6	TERMINAL	BRASS	3	Ag-PLATING	<1.5: $\pm 0.1\text{mm}$ >1.5~5.0: $\pm 0.25\text{mm}$ >5.0: $\pm 0.3\text{mm}$	ANGULAR $\pm 1^{\circ}$	A1	2026.5.29	增加黑色底座	BY	
5	CASE	PA66	1	WHITE/BLACK			NO	DATE	REVISIONS	BY	APPD
4	SHRAPNEL	PHOSPHOR BRONZE	1		TITLE: TACY SWITCH		UNIT : MM		ROHS	DWN	
3	CONTACT	COPPER ALLOY	1		MODEL: RT-M3-03D2P01A030-A		SCALE: 1:1		COMPLIANT	CHK'D	
2	COVER	PBT	1	BLACK	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司		APPD		PRO.AGL:  		REV :A1
1	STEM	PA66	1	RED							
NO.	PART NAME	MATERIAL	QTY	FINISHING							