







- 1.电路CIRCUIT: ON/OFF;  
2.快插端子QUICK CONNECTOR TYPE;  
单刀单掷(SINGLE POLE DOUBLE THROW);  
3.额定值RATING:16A 125/250VAC (UL;C-UL);  
12A 125/250VAC (UL;C-UL);  
16(4)A 250V~T125/55(ENEC17;NEMKO;CQC;CB)  
4.柄的颜色ACTUATOR COLOR:黑色BLACK  
基座的颜色HOUSING COLOR:黑色BLACK  
5.柄的印字形式ACTUATOR PRINTING:白色"O/-" WHITE COLOR  
6.所有部件均使用环保材料  
ALL MATERIALS USE IN CONFORMIY WITH THE RoHS DIRECTIVE


电话 : 0769-82310511-867  
邮箱 : hooya89@hooya.hk

PANEL CUTOUT DIMENSION



| PANEL THICKNESS | X                                     | Y                                     |
|-----------------|---------------------------------------|---------------------------------------|
| 0.8~1.2mm       | 19.2 <sup>+0</sup> <sub>-0.1</sub> mm | 12.9 <sup>+0.1</sup> <sub>-0</sub> mm |
| 1.3~2.0mm       | 19.4 <sup>+0</sup> <sub>-0.1</sub> mm | 12.9 <sup>+0.1</sup> <sub>-0</sub> mm |
| 2.1~2.5mm       | 19.8 <sup>+0</sup> <sub>-0.1</sub> mm | 12.9 <sup>+0.1</sup> <sub>-0</sub> mm |



|    |             |    |             |                        |           |                                                                                                                          |         |        |                   |                   |       |             |      |
|----|-------------|----|-------------|------------------------|-----------|--------------------------------------------------------------------------------------------------------------------------|---------|--------|-------------------|-------------------|-------|-------------|------|
|    |             |    |             | DIMENSIONAL TOLERANCES |           | APPROVED                                                                                                                 | CHECKED | DESIGN | DRAWN             | ALL SIZE ARE IN   | MM    |             |      |
|    |             |    |             | RANGE                  | TOLERANCE |                                                                                                                          |         |        | LMC<br>2026.01.17 | SCALE             | NO    |             |      |
|    |             |    |             | 20≤                    | ±0.40     |                                                                                                                          |         |        |                   | MAT'L             | ***   |             |      |
|    |             |    |             | 10~20                  | ±0.30     |                                                                                                                          |         |        |                   | MATERIAL NO.      |       | DRAWING NO. | REV. |
|    |             |    |             | ≤10                    | ±0.20     |  legion-switch.com<br>东莞市六钩电子五金有限公司 |         |        |                   | SS11-BBIWG-RA20-R | ***** | A0          |      |
| NO | DESCRIPTION | NO | DESCRIPTION | ANGLES                 | ±1'       |                                                                                                                          |         |        |                   |                   |       |             |      |