






RoHS
Compliant

6	7			
REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		



PIN NO.	DIM. A	DIM. B	DIM. C
28	18.10	13.50	14.57
29	18.60	14.00	15.07
30	19.10	14.50	15.57
31	19.60	15.00	16.07
32	20.10	15.50	16.57
33	20.60	16.00	17.07
34	21.10	16.50	17.57
35	21.60	17.00	18.07
36	22.10	17.50	18.57
37	22.60	18.00	19.07
38	23.10	18.50	19.57
39	23.60	19.00	20.07
40	24.10	19.50	20.57
41	24.60	20.00	21.07
42	25.10	20.50	21.57
43	25.60	21.00	22.07
44	26.10	21.50	22.57
45	26.60	22.00	23.07
46	27.10	22.50	23.57
47	27.60	23.00	24.07
48	28.10	23.50	24.57
49	28.60	24.00	25.07
50	29.10	24.50	25.57
51	29.60	25.00	26.07
52	30.10	25.50	26.57
53	30.60	26.00	27.07
54	31.10	26.50	27.57
55	31.60	27.00	28.07
56	32.10	27.50	28.57
57	32.60	28.00	29.07
58	33.10	28.50	29.57
59	33.60	29.00	30.07
60	34.10	29.50	30.57

NOTES:

- 1.MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL94V_0,COLOR:BLACK.
CONTACT: COPPER ALLOYS.
- 2.PLATING:
UNDERPLATE: NICKEL.
CONTACT AREA: TIN OVER NICKEL.
- 3.MULTIMEDIA CARD COMPATIBLE

X. ±0.50	X° ± 2°	UNITS mm	广东创粤科技有限公司			
.X ±0.30	.X° ± 1°					
.XX ±0.10	.XX° ± 0.5°	MAT'L /	TITLE: FPC 0.5PH H1.5前掀14P			
.XXX ± 0.05						
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH /	FPC-14P-0.5PH1.5H-30258		DWG NO.:	
		Q'TY /	CHKD:		SCALE SHEET REV. 1/1 1/1 A1	
			DR:			