










SPECIFICATION

- 1.Rating : DC 20V 10A.
- 2.Contact resistance: $\leq 50\text{m}\Omega$.
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
- 4.Withstanding voltage: 500VAC .
- 5.Insertion and extraction force: 3-30N.
- 6.life test: 5,000 cycles.
- 7.Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
- 8.Sign "*" is importance dimension.

邮箱: hooya89@hooya.hk
电话: 0769-82310511-867



DC MATE PLLG

					TOLERANCE UNLESS SPECIFIED					
6	COVER PLATE	SUS	1	Ni-PLATED	<1.5: $\pm 0.1\text{mm}$	ANGULAR	1			
5	SHELL	SUS	1		>1.5~5.0: $\pm 0.25\text{mm}$	$\pm 1^{\circ}$	NO	DATE	REVISIONS	BY APPD
4	FLAT PIECE	BRASS	1	Sn-PLATED	>5.0: $\pm 0.3\text{mm}$					
3	SPRING	PHOSPHOR BRONZE	1	Ag-PLATED	TITLE: DC JACK		UNIT : MM		ROHS	DWN
2	PIN	ZINC ALLOY	1	Au-PLATED	MODEL: DC-044Z-2.5-PU-04		SCALE: 1:1		COMPLIANT	CHK'D
1	CASE	PA10T	1	BLACK	 HOOYAELEC.COM 皓宇 东莞市弘皓电子有限公司				APPD	
NO.	PART NAME	MATERIAL	QTY	FINISHING			PRO.AGL: 		REV :A0	