






P.C.B LAYOUT

SPECIFICATION

- 1.Rating : DC42V 0.1A.
- 2.Contact resistance: $\leq 50m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC250V).
- 4.Withstanding voltage: 500VAC .
- 5.Operating Force: $35\pm 20gf$.
- 6.life test: 200000 cycles.
- 7.Operation temperature range: $-25^{\circ}C \sim 85^{\circ}C$.
- 8.Sign "*" is importance dimension.

电话 : 0769-82310511-867

邮箱 : hooya89@hooya.hk



				TOLERANCE										
				UNLESS SPECIFIED		A1	2026.4.29	品名更新为RT-M3-07B3P10A030-A-0.1						
				<1.5: ±0.1mm		ANGULAR	A0	2025.8.9	首次发行		MLQ			
				>1.5~5.0: ±0.25mm		±1°	NO	DATE	REVISIONS		BY		APPD	
				>5.0: ±0.3mm										
						TITLE: Micro Switch		UNIT : MM		ROHS	DWN			
						MODEL: RT-M3-07B3P10A030-A-0.1		SCALE: 1:1		COMPLIANT	CHK'D			