

型号	CKT	A	B
XY-MX3.0-02A21	2*1	0.00	6.00
XY-MX3.0-04A21	2*2	3.00	9.00
XY-MX3.0-06A21	2*3	6.00	12.00
XY-MX3.0-08A21	2*4	9.00	15.00
XY-MX3.0-10A21	2*5	12.00	18.00
XY-MX3.0-12A21	2*6	15.00	21.00
XY-MX3.0-14A21	2*7	18.00	24.00
XY-MX3.0-16A21	2*8	21.00	27.00
XY-MX3.0-18A21	2*9	24.00	30.00
XY-MX3.0-20A21	2*10	27.00	33.00
XY-MX3.0-22A21	2*11	30.00	36.00
XY-MX3.0-24A21	2*12	33.00	39.00

Technical Index:

1. Temperature range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. Rated voltage: 600V, AC, DC.
3. Rated current: 5.0A AC, DC.
4. Contact resistance: $\leq 20\text{m}\Omega$.
5. Withstanding voltage: 1500V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.

序号	品名	材质
1	MX3.0双排弯针WTB胶芯	PA66 UL94V-0 黑色
2	MX3.0双排弯针WTB端子	铜合金/表面镀锡

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	TITLE: MX3.0MM WAFER DIP TYPE		
X.X $\pm$ 0.30	X.* $\pm$ 5°	Alex	DWG NO. XY-MX3.0-NA21		
X.XX $\pm$ 0.25	X.X° $\pm$ 1°	Jack	PROJ.  CUSTOMER DRAWING		
X.XXX $\pm$ 0.15		Can	SIZE A4	SCALE 1:1	SHEET 1/1 REV. A

PCB.WELDING DRAWING (TOLERANCE: ± 0.05)