



RoHS
Compliant

6	7			
REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		

NOTES:





1.MATERIAL:

HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL94V_0,COLOR: BLACK.
CONTACT: COPPER ALLOYS.
COVER: COPPER ALLOYS OR STEEL.

2.PLATING:

UNDERPLATE: NICKEL.
CONTACT AREA: GOLD OVER NICKEL.
SOLDER AREA: TIN OVER NICKEL.

3.MULTIMEDIA CARD COMPATIBLE






X. ±0.50	X° ±2°	UNITS	广东创粤科技有限公司			
.X ±0.30	.X° ±1°	mm	SD 自弹卡座脚朝内外壳镀镍			
.XX ±0.10	.XX° ±0.5°	MAT'L	TITLE:			
.XXX ±0.05			SD-H2.7-30223			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD			FINISH		DWG NO.:	
			Q'TY		CHKD:	
					DR:	
					SCALE SHEET REV.	
					1/1 1/1 A1	



RoHS
Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		




1. 材质要求:

- 1.1 纸箱材质要求为K=K; 外形尺寸为34*34*22CM(1.4Kset)。
- 1.2 卷盘的材质为PS; 卷盘的外形尺寸为 $\phi 330 \times 48.2$;
- 1.3 卷带的材质为PS; 卷带的外形尺寸为12960*44.0*3.4mm


2. 包装要求:

- 2.1 将卷带放入包装机后, 前空5PCS, 后放产品350PCS, 再后空5PCS; 上带留300MM长度。
- 2.2 将包装好的产品从包装机上取下并包装好;
- 2.3 把累叠好的4盘(1.4Kset/箱)粘贴好标签放入纸箱。
- 2.4 把包装好的成品打包封箱, 并在纸箱外贴上标签



纸箱规格1: 340*340*210

NO. 4



NO. 3

X. ± 0.50	X.° $\pm 2^\circ$	UNITS mm	广东创粤科技有限公司	
.X ± 0.30	.X° $\pm 1^\circ$		SD 自弹卡座脚朝内外壳镀镍	
.XX ± 0.10	.XX° $\pm 0.5^\circ$	MAT'L	TITLE:	
.XXX ± 0.05			SD-H2.7-30223	DWG NO.:
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH	CHKD:	SCALE SHEET REV.
		Q'TY	DR:	1/1 1/1 A1