




AFTER MATING



Ø3.50 4 POLE PLUG



PJ -3 R 010 A-4 N G D 01

Type
PJ=Phone Jack

Specification
3=Ø3.5mm

Angle
R=90°

Serial code

Detail
A:Mid-Mount1.9






Number Of Contacts
4=TRRS

Other



Termipoint
D=DIP

Contact Plated
G=Gold

Housing Colour
N=Black



CIRCUIT DIAGRAM



PCB REFERENCE DIAGRAM
TOLERANCE:±0.05

G-Switch Specification:

- 1.Rated load: 0.5A.30V DC
- 2.Insulation resistance: 100MΩ min
- 3.Withstand voltage: 500V AC/min
- 4.Contact resistance: 30mΩ max
- 5.Durability cycle: 5,000 Cycles
- 6.Insertion and extraction force: 3-30N
- 7.Operating temperature range: -40°C ~ +85°C

2	TRANSFER TERMINAL	1	SUS304	G/F OVER NI UNDERPLATING
1	HOUSING	1	PA9T	BLACK
NO.	DESCRIPTION	QTY	MATERIAL	PLATED & COLOR



SCALE:	UNIT: mm	Title: Horizontal Ø3.5mm Phone Jack NO 5Pin Mid-Mount1.9 L=12.70mm DIP			
SIZE: A4		Molde Code: PJ-3R010A-4NGD01			
Unless otherwise General tolerance:		DRAWN	CHECKED	APPROVED	DATE
X.x ±0.38 X.xx ±0.25 Angles ±3°		Xia	Chen	Chen	2025.09.15



REV: A0 SHEET: 1/1