





Technical Index:

1. Temperature range: -25°C~85°C.
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 5A AC, DC.
4. Contact resistance: ≤20mΩ.
5. Dielectric withstanding voltage: 1500V AC/minute.
6. Insulation resistance: ≥1000MΩ.
7. Apply to gauge: AWG#20~#24.

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: MX3.0MM TERMINAL	
X.X±0.30	X.*±5°	CHK.	Jack	DWG NO. XY-MX3.0-31-M	
X.XX±0.25	X.X*±1°	DRA.	Can	PROJ.  CUSTOMER DRAWING	
X.XXX±0.15		SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A