






技术指标:

1. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. 额定电流: 5.0A AC DC.
3. 额定电压: 250V AC DC.
4. 耐压: 1000V AC/minute.
5. 接触电阻: $\leq 20\text{m}\Omega$.
6. 绝缘电阻: $\geq 1000\text{M}\Omega$.


材质:

1. 胶芯: LCP UL94V-0 黑色
2. 端子: 铜合金/表面镀锡
3. 焊片: 铜合金/表面镀锡
4. 不锈钢吸盖: 不锈钢

型号	CKT	A	B
XY-MX3.0-2A51	2*1	0.00	6.65
XY-MX3.0-4A51	2*2	3.00	9.65
XY-MX3.0-6A51	2*3	6.00	12.65
XY-MX3.0-8A51	2*4	9.00	15.65
XY-MX3.0-10A51	2*5	12.00	18.65
XY-MX3.0-12A51	2*6	15.00	21.65
XY-MX3.0-14A51	2*7	18.00	24.65
XY-MX3.0-16A51	2*8	21.00	27.65
XY-MX3.0-18A51	2*9	24.00	30.65
XY-MX3.0-20A51	2*10	27.00	33.65
XY-MX3.0-22A51	2*11	30.00	36.65
XY-MX3.0-24A51	2*12	33.00	39.65

PCB.WELDING DRAWING (TOLERANCE: ± 0.05)

DIMENSION IN mm		厦门市辛译精密电子有限公司				
TOLERANCE UNLESS OTHERWISE SPECIFIED		Xiamen XinYi Xyeconn Electronics Co.,Ltd				
X.X±0.30	X."±5°	APR.	Alex	TITLE: MX3.0MM 双排母座		
X.XX±0.25	X.X"±1°	CHK.	Jack	DWG NO. XY-MX3.0-NA51		
				PROJ.		
X.XXX±0.15		DRA.	Can	CUSTOMER DRAWING		
				SIZE A4	SCALE 1:1	SHEET 1/1



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
X.X±0.30	X.*±5°	APR. Alex	TITLE: MX3.0MM 连接器			
X.XX±0.25	X.X'±1°	CHK. Jack	DWG NO. XY-MX3.0-NA51			
X.XXX±0.15		DRA. Can	PROJ. 	CUSTOMER DRAWING		
			SIZE A4	SCALE 1:1	SHEET 1 / 1	REV. A