






技术指标(Technical Index):

1. 工作温度(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. 额定电压(Rated voltage): 50V DC/AC(rms).
3. 额定电流(Rated current): 1.5A, AC/DC(AWG#28).
4. 接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
5. 耐压值(Dielectric withstanding voltage): 500V AC/minute.
6. 绝缘电阻(Insulation resistance): $\geq 100\text{M}\Omega$.
7. 适用线规(Apply to gauge): AWG28#~AWG30#
(O.D 0.5mm~0.7mm).

P/N	材质	镀层
XY-PE1.2-31-GAU	磷青铜	镀金1u"
XY-PE1.2-31-GTP		镀锡



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 1.2Pitch 2.54mm间距连接器	
X.:±0.50	±1°	CHK.	Jack	DWG NO. XY-PE1.2-31-GX	
X.X:±0.20		DRA.	Can	CUSTOMER DRAWING	
X.XX:±0.10		SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A