

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.19	桑葚
A1	N/A		产品尺寸变更，图面升级整理图面	2025.12.23	阿树

Specifications(规格):
1.Voltage rating(额定电压):50V AC DC
2.Current rating(额定电流):1.0A AC/DC
3.Withstanding voltage(耐压值):≥500V AC/minute
4.Insulation resistance(绝缘电阻):100MΩ Min
5.Contact resistance(接触电阻):30mΩ Max
6.Temperature range(使用温度):-40℃~+125℃

PART NO.:

X1010 H-13-N0
① ② ③ ④

- ①Series No
②Category:H-HSG
③Row No.Pin No:XX-02~15Pin
④Material:N0-PA66 UL94V-0

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	5.00	2.00	09	8.00	11.00	4.30
03	2.00	5.00	2.00	10	9.00	12.00	6.15
04	3.00	6.00	2.00	11	10.00	13.00	
05	4.00	7.00	3.40	12	11.00	14.00	
06	5.00	8.00	4.30	13	12.00	15.00	8.10
07	6.00	9.00		14	13.00	16.00	
08	7.00	10.00		15	14.00	17.00	

X1010H-13-N0	PA66	X1010W	X1010T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE: 1.0mm Crimp Style Housing		
PART NO.: X1010H-13-N0		
DWG NO.: X-X1010H-13-N0		
SCALE N/A	PAGE 1/1	REVISION A1

XKB INDUSTRIAL PRECISION CO.,LIMITED