



Specifications:

规格:


Voltage rating:600V AC/DC
 额定电压: 600V AC/DC
 Withstanding voltage:2500V AC/minute
 耐受电压: 2500V AC/分钟
 Temperature range:-40℃~+125℃
 温度范围: -40℃~+125℃
 Insulation resistance:1000MΩ min
 绝缘电阻: 1000MΩ Min
 Contact resistance:5mΩ Max
 接触电阻: 5mΩ Max

K 792100 H - 05 - N0
 ① ② ③ ④ ⑤ ⑥


- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Row No.Pin No:XX-01~05 Pin
- 5.Material:N0-PA66 UL 94V-0
- 6.Color:B-Black ;R-Red ;Blank-Natural




Guide Key : Inside Color : Natural



Guide Key : Right Side Color : Black



Guide Key : Left Side Color : Black



PART NO	DIM A	DIM B
01	8.00	/
02	15.50	7.92
03	23.42	15.84
04	31.34	23.76
05	39.26	31.68

K792100H-05-N0	PA66	K792100H	K792100H
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 7.92mm Automobile connector
DWN		VIEW:	PART NO.: K792100H-05-N0
CHKD		UNIT: mm/in	DWG NO.: X-K792100H-05-N0
APPD		SIZE: A4	

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δx					ANGULAR ±5°
Δx					L ≤ 4 ±0.2
Δx					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0