

RoHS

REV.

ECN.#

DESCRIPTION

NAME




DATE

AO

NEW RELEASE

HZP

2023.01.02

SEC A-A
Scale 2:1Scale 2:1
Long Cover type

NOTE:

1.MATERIAL




- 1.1: HOUSING: LCP UL94-V0 COLOR:WHITE
1.2: ACTUATOR: LCP OR PA UL94-V0 COLOR:BLACK.
1.3: CONTACT: PHOSPHOR BRONZE.
1.4: LEG: PHOSPHOR BRONZE.

2.PLATING


- 2.1: CONTACT: SEE PART NUMBER.
2.2: LEG: MATTE TIN PLATING OVER NICKEL.

3.RATING:

- 3.1: OPERATING VOLTAGE: 30V AC/DC.
3.2: CURRENT RATING: 0.2A AC/DC.
3.3: OPERATING TEMPERATURE:-55~C~+85~C.



Applicable FPC

FPC/FFC Insert Direction
Recommended P.C.B Layout

No. of Contacts	Dimension					
	A	B	C	D	E	F
09	4.90	1.80	2.40	3.03	4.35	3.00
11	5.50	2.40	3.00	3.63	4.95	3.60
13	6.10	3.00	3.60	4.23	5.55	4.20
15	6.70	3.60	4.20	4.83	6.15	4.80
17	7.30	4.20	4.80	5.43	6.75	5.40
19	7.90	4.80	5.40	6.03	7.35	6.00
21	8.50	5.40	6.00	6.63	7.95	6.60
23	9.10	6.00	6.60	7.23	8.55	7.20
25	9.70	6.60	7.20	7.83	9.15	7.80
27	10.30	7.20	7.80	8.43	9.75	8.40
29	10.90	7.80	8.40	9.03	10.35	9.00
31	11.50	8.40	9.00	9.63	10.95	9.60
33	12.10	9.00	9.60	10.23	11.55	10.20
35	12.70	9.60	10.20	10.83	12.15	10.80
37	13.30	10.20	10.80	11.43	12.75	11.40
39	13.90	10.80	11.40	12.03	13.35	12.00
41	14.50	11.40	12.00	12.63	13.95	12.60
43	15.10	12.00	12.60	13.23	14.55	13.20
45	15.70	12.60	13.20	13.83	15.15	13.80
47	16.30	13.20	13.80	14.43	15.75	14.40
49	16.90	13.80	14.40	15.03	16.35	15.20
51	17.50	14.40	15.00	15.63	16.95	15.60

Long Cover type

MILLIMETERS	INCH
X* ±2*	X* ±2*
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBilai Metal Plastic Technology Co.,Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBilai Metal Plastic Technology Co.,Ltd

东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

	TITLE		0.3PITCH 1.0H ZIF/ 前插后掀式		DR		
	PART NO.		111310532-XX		CHKD		
	PRO J.		PAGE	1/2	UNITS	mm	APPD
HE			SIZE	A4	SCALE	1:1	DIS NO.