



SPECIFICATIONS
 Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω Min
 Contact Resistance: 20m Ω Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$
 Contact Material: Brass
 Standard: PA6T
 Insrlator Material: Polyester
 Contact Plating: Gold Flash
 Max.Processing Temp: 200 $^{\circ}$ C for30-60seconds
 (255 $^{\circ}$ C for5seconds)



A-A SECTION



RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

尺寸对列表		
H	PC	L
5.7	2.8	8.0

2	接触	铜	镀金	
1	基座	PA6T	黑色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE	筒牛	
			料 号 PART NO	HC-JN200-5. 7L-2x8PZ-02A-Y	
一般公差 TOLERANCE		比 列 SCALE	1 : 1		
X : ±0.30 X° : ±5° X.X : ±0.25 X.X° : ±1° X.XX : ±0.20 X.XX° : ±0.5°		单 位 UNIT	MM		
		张 数 PART NO	1 OF 1		
		版 本 REV	A		
		制 图 DRAW	AhYe		
		审 核 CHECKED	夏操云		
		批 准 APPROVE	赵亮亮		