



| REVISIONS |         |          |                 |            |        |
|-----------|---------|----------|-----------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | /          | /      |
| A1        | N/A     |          | 图面升级整理图面        | 2025.05.22 | 阿树     |



PART NO.:

X02 37 F I 7 B 1  
① ② ③ ④ ⑤ ⑥ ⑦



- ①Series NO.  
②Row No.Pin No.XX-09;15;25;37  
③Welding Board Angle :F-Female  
④T: Tradutional C: Car-pin  
⑤Planting Category: 1:1U' 2:2U' 3:3U' 4:5U'  
5:15U' 6:30U' 7:AuSn  
⑥Color:B-BLACK W-White BL-Blue  
⑦1:TYPE-1; 2:TYPE-2; 5:TYPE-5; 7:TYPE-7

#### Specifications:

规格:

- 1.Voltage rating:250VAC/DC  
额定电压: 250V AC/DC
  - 2.Current rating:1A AC/DC  
额定电流: 1A AC/DC
  - 3.Withstanding voltage:500V AC/minute  
耐受电压: ≥500V AC/分钟
  - 4.Temperature range: -55℃--+105℃  
温度范围: -55℃--+105℃
  - 5.Insulation resistance:1000MΩMIN  
绝缘电阻: ≥1000MΩ
  - 6.Contact resistance:30mΩMax  
接触电阻: ≥30mΩ
- Material:  
材料:  
7.Rubber core:PBT UL94V-0  
胶芯: PBT UL94V-0  
8.The iron shell:SPCC Nivkel Plating/Tin Plating/Gold Plating  
铁壳: SPCC,镀镍/镀锡/镀金  
B、成品不能有弯针, R角不一致等不良。

| NUMBER OF POSITIONS | DIMENSION |        |        |        |
|---------------------|-----------|--------|--------|--------|
|                     | A±0.25    | B±0.13 | C±0.38 | D±0.25 |
| 9                   | 30.80     | 24.99  | 16.35  | 19.28  |
| 15                  | 39.20     | 33.32  | 24.75  | 27.51  |
| 25                  | 53.05     | 47.04  | 38.35  | 41.28  |
| 37                  | 69.40     | 63.50  | 54.75  | 57.71  |



| 铆合方式 | TYPE-1:铆合 | TYPE-2:前铆实心螺母 | TYPE-7:后铆鱼叉 | TYPE-5:铆鱼叉锁螺丝 |
|------|-----------|---------------|-------------|---------------|
| 图示   |           |               |             |               |

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



|           |    |             |                       |
|-----------|----|-------------|-----------------------|
| DESIGN    | 阿树 | VIEW:       | MODEL TYPE: D-SUB     |
| CHECKED   |    | UNIT: mm/in | PART NO.: X0237FT7B1  |
| APPROVED  |    | SIZE: A4    | DWG NO.: X-X0237FT7B1 |
| SCALE N/A |    |             | PAGE 1/1              |
|           |    |             | REVISION A1           |