

G

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester
Contact Plating: Gold Flash
Max.Processing Temp: 200 $^{\circ}$ C for 30-60seconds
(255 $^{\circ}$ C for 5seconds)

RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

<http://hcdz2017.com/>