




\* ROHS COMPLIANT




Specification

MATERIAL:  
Insulator: High Temperature Thermoplastic, (塑胶: 聚酰CP, 防火等级UL 94V-0)  
Contact: Copper Alloy(铜) T=0.15mm  
基板材料 PA

PLATING:  
Contact: Plated 50u" Ni Overall Contact Au 3U, pad TIN  
(端子: 镀层50u, 接触点3u, 焊点镀50u最少)

Electrical:  
Current Rating : 2Amps.max(额定电流: 2A最大)  
Voltage Rating : 5V AC/DC(额定电压: 5V AC/DC)  
Ambient Temperature Range : -20°C~+80°C(工作温度: -20度~+80度)  
Storage Temperature Range : -20°C~+80°C(工作温度: -20度~+80度)  
Ambient Humidity Range : 95% R.H. Max.(相对湿度: 95%以上)  
Contact Resistance: 100mΩ max(端子接触电阻: 100mΩ最大)  
Insulation Resistance: 1000MΩ min./50VDC(绝缘电阻: 1000兆欧最小)  
产品存储温度: 260度  
Mating Cycles: 5000Min Insertions(寿命: 5000次)

| PIN NO. | PIN NAME                |
|---------|-------------------------|
| C1      | Supply Voltage Vcc      |
| C2      | Reset (RST)             |
| C3      | Clock (CLK)             |
| C4      | N/A                     |
| C5      | Ground                  |
| C6      | Programming Voltage Vpp |
| C7      | I/O                     |
| C8      | N/A                     |



| REVISION NO. | ECR NO. | DESCRIPTION | MARK | DATE |
|--------------|---------|-------------|------|------|
| 1            |         |             |      |      |
| 2            |         |             |      |      |
| 3            |         |             |      |      |
| 4            |         |             |      |      |
| 5            |         |             |      |      |
| 6            |         |             |      |      |

浙江创都电子科技有限公司

|                                                                                                                                            |                                       |                                         |                     |
|--------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------|-----------------------------------------|---------------------|
| DIMENSIONS IN: mm<br>UNLESS OTHERWISE SPECIFIABLE<br><br>DIMENSION TOLERANCE<br>X.X ± 0.38<br>X.XX ± 0.25<br>X.XXX ± 0.10<br>ANGULAR: ± 1° | PRODUCT NAME :<br>Sim 3.0H卡托式 PUSH带卡套 | DRAWING:                                | DATE:<br>2016/05/10 |
|                                                                                                                                            | PRODUCT NO. :<br>CAX-SIM-KT8PWZ-Z     | CHECK:                                  | DATE:<br>2016/05/11 |
|                                                                                                                                            | DRAWING NO. :                         | APPROVED:                               | DATE:<br>2016/05/11 |
|                                                                                                                                            |                                       | SCALE: NA DWG ID: P D REV.: A PAGE: 1 号 |                     |