


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		新增尺寸，图面升级整理图面	2024.9.25	阿树
A2	ECN-P-2026082102	(A2)X2	公差变更	2026.08.21	山楂



- SPECIFICATIONS
- Voltage rating: 250V AC/DC
 - Current rating: 2A AC/DC
 - Withstanding Voltage: 800V AC/minute
 - Temperature range: -40°C ~ +125°C
 - Insulation resistance: ≥ 1000MΩ
 - Contact resistance: ≤ 20mΩ

PART NO.:

X2011 I F-P SN-A
① ② ③ ④ ⑤ ⑥

- ① Series Number.
② Category: T-terminal
③ Shape: F-Female Terminal
④ Material: P-Phosphor bronze
⑤ Plating Category: SN-Bright Tin Plating
⑥ TYPE: A Type

X2011TF-PSN-A	Phosphor Bronze	AWG#30~24	X2011HM
PART NO	Material	Wire Range	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	山楂	VIEW:	MODEL TYPE: 2.00mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X2011TF-PSN-A
APPROVED		SIZE: A4	DWG NO.: