

G

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω /Min
Contact Resistance: 20m Ω /Max
Withstanding Voltage: AC 500V
Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester
Contact Plating: Gold Flash
Max.Processing Temp: 200 $^{\circ}$ C for30-60seconds
(255 $^{\circ}$ C for5seconds)

RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

[p://hcdz2017.com/](http://hcdz2017.com/)